

POLY-MAGIC-WHEEL

A mirror finish in corners without polishing additives (dry polishing)

The POLY-MAGIC-WHEEL is designed for finishing and dry polishing in corners, producing up to a perfect mirror finish in just two steps. These discs are made of highly compressed fleece material and are made in a sophisticated production process using compressed single flaps that are strengthened by being impregnated with foam. This special process allows considerably more abrasive material to be used than on conventionally wound "unitized wheels and discs."

The POLY-MAGIC-WHEEL is ideal for grinding and polishing bead and corner welds. It may only be used frontally.

POLY-MAGIC-WHEEL Specifications

Dimensions	6-1/2" dia. x 1/2" material thickness x 7/8" arbor
Max. speed	5000 RPM
Ideal speed	3000 to 4000 RPM
Grits	A/80, B/900

Ideal for speed-controlled angle grinders

POLY-MAGIC-WHEEL Ordering Information

Part No.	Grit	Usage	Qty.
96720	Grit A (80 grit)	Initial grinding & leveling welds (red)	5 pk.
96721	Grit B (900 grit)	Polishing to a perfect mirror finish (gray)	5 pk.



Ideal for
polishing
in corners

TIPS & TRICKS


Polishing corner welds with the POLY-MAGIC-WHEEL

Obtaining good polish quality when finishing corner welds is difficult, especially for the fabrication of railings. The POLY-MAGIC-WHEEL was designed to help you more easily produce a truly perfect finish in these applications. This highly compacted fleece disc was designed specifically for grinding and polishing bead and corner welds. The POLY-MAGIC-WHEEL disc can reduce the time required for this work to a minimum, and the result can only be described as a minor miracle.

Carry out the initial grinding and leveling of welds with the red disc, grit A (80 grit). If the weld is very coarse it is a good idea to use the TRIMTEX® disc first.

Then polish to a mirror finish using the POLY-MAGIC gray disc, grit B (900 grit). These discs are very aggressive; they save a lot of working time and the result is sensational. No polishing compounds or creams are required for polishing with the POLY-MAGIC-WHEEL (dry polish).

Mirror finish in 3 steps:



1.

TRIMTEX® for coarse welds



2.

POLY-MAGIC-WHEEL A (80 grit)



3.

POLY-MAGIC-WHEEL B (900 grit)